

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2016066163](#)
Status: **Active**
Overview: High-Current, Universal-Clamp Terminal Blocks
Description: High Current Universal Clamp Terminal Block, 35.00mm DIN-rail Mount, 150.0A / 600V, Grey Housing and Cover, 3 Circuits

Documents:

[3D Model](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Drawing \(PDF\)](#) [Product Literature \(PDF\)](#)

General

Product Family	Terminal Blocks
Series	201606
Application	Wire-to-Wire
Component Type	One Piece
Overview	<u>High-Current, Universal-Clamp Terminal Blocks</u>
Product Literature Order No	987651-7108
Product Name	Universal Clamp
Type	Universal Clamp
UPC	78172551095

Physical

Circuits (Loaded)	3
Circuits (maximum)	3
Color - Resin	Grey
Entry Angle	Horizontal
Lock to Mating Part	None
Material - Metal	Aluminum
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Polyamide
Number of Rows	3
Orientation	Vertical
Panel Mount	No
Pitch - Mating Interface	N/A
Polarized to Mating Part	N/A
Stackable	No
Temperature Range - Operating	-40°C to +105°C
Termination Interface: Style	Screw
Wire Size AWG	1/0-6, 6+6, 8+8+8
Wire Size mm ²	13.00+13.00, 13.00-53.00, 8.30+8.30+8.30

Electrical


Current - Maximum per Contact	150.0A
Voltage - Maximum	600V

Material Info

Engineering Number	MX-KE61-03
--------------------	------------

Reference - Drawing Numbers

Sales Drawing	2016066163-000
---------------	----------------



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[201606 Series](#)