

Precision pointer micrometer

MAHR 40 T/1003



Application:

For quick testing of parts from series production.

Version:

- Adjustable tolerance marks
- Carbide measuring faces
- Strong steel bracket
- Movable measuring probe for lifting the anvil

Delivery:

In case, precision pointer included



| | |
|---|------------------|
| Art. no. | 31472 125 |
| Min./max. length measuring range | 25-50 mm |
| Indicating calliper measuring range | +/- 0.05 mm |
| Digit increment, micrometer | 0.01 mm |
| Digit increment, indicating calliper | 0.001 mm |
| Micrometer error limit | 0.002 mm |
| Indicating calliper error limit | 0.001 mm |
| Measuring spindle increments | 0.5 mm |
| Spindle clamping | Yes |
| Measurement force | 6.5 N |
| Measuring surface diameter | 7.5 mm |
| Calibration Group | AN |
| DIN | 863 |

EAN-Code

4059 192004682