

Platform trolley series 500 with front wall, zinc-plated

Loading area made of MDF board, load capacity 500 kg



Execution:

- Loading area and front wall made of melamine-coated MDF board
- Loading area height 260 mm
- Push handle made of 25 mm steel tubing
- 2 fixed castors and 2 castors made of solid rubber 200 x 50 mm
- Galvanised
- The 500 series also includes table trolleys, cabinet trolleys, platform trolleys with front walls and other variants.



Art. no.	50250 019
Brand	KONGAMEK
Manufacturer Part Number	KM532-2B
Colour	Silver coloured
Load-carrying capacity	500 kg
Material of loading surface	Medium density fibreboard
Type	With front wall
Length	1000 mm
Width	700 mm
Height	900 mm
Number of fixed rollers	2
Loading surface length	1000 mm
Loading surface size	1000 x 700 mm
Number of steering rollers	2
Loading-surface height	260 mm
Loading-surface width	700 mm
Length x width x height	1000 x 700 x 900 mm
With wheel lock	Yes
Wheel width	50 mm
Wheel diameter	200 mm
Material of wheel	Solid rubber
Surface	Zinc plated
Gross Weight	27.500 kg
Product Group	5AT

EAN

73500503576 10