

## Workbench trolleys

Working height 840 mm, with 4 drawers and 1 open compartment

### Application:

The mobile workstation with versatile options for use.

### Execution:

- Welded sheet steel construction equipped with one workbench top panel made of solid beechwood, 40 mm thick
- Suitable insert material for drawers, see from no. 50485 060-265 and from no. 50537 610-695
- Other equipment options available at extra cost: SOFT-CLOSE for drawers, see no. 50392 005, ELECTRONIC CODE combination lock, see no. 50392 010

### Advantage:

- When you buy this product, you plant a tree and also receive a tree certificate!
- When you buy this product, you plant a tree and also receive a tree certificate!



<b>Art. no.</b>	<b>50285 211</b>
<b>Brand</b>	HK
<b>Manufacturer Part Number</b>	50285211
<b>Number of fixed rollers</b>	2 PCS
<b>Working height</b>	840 mm
<b>Number of steering rollers</b>	2 PCS
<b>Worktop width</b>	1155 mm
<b>Number of drawers</b>	4 PCS
<b>Worktop height</b>	40 mm
<b>Worktop depth</b>	700 mm
<b>Pullout type</b>	Partial extension
<b>On castors</b>	Yes
<b>Moving device, can be lowered</b>	No
<b>Colour of front</b>	Anthracite grey RAL 7016
<b>Cabinet colour</b>	Light grey RAL 7035
<b>With single pull-out safety brake</b>	Yes
<b>Surface</b>	Powder-coated
<b>With wheel lock</b>	Yes
<b>Load-carrying capacity</b>	820 kg
<b>Wheel diameter</b>	200 mm
<b>Type</b>	mobile
<b>Lock type</b>	DOM® locking system
<b>Material of worktop</b>	Solid beech
<b>Drawer front height</b>	1 x 60 mm, 1 x 90 mm, 1 x 150 mm, 1 x 180 mm
<b>Material</b>	Sheet steel
<b>Drawer width (inner dimension)</b>	450 mm
<b>Drawer width (inner dimension) x drawer depth (inner dimension)</b>	450 x 600 mm
<b>Drawer depth (inner dimension)</b>	600 mm
<b>Load-carrying capacity per drawer</b>	100 kg
<b>Material of wheel</b>	Solid rubber
<b>Central locking</b>	Yes
<b>Gross Weight</b>	109.000 kg
<b>Product Group</b>	501

### EAN

4053625403301