

PTC 70 soldering iron, electronically controlled

75 W output



Application:

For the most delicate soldering work and for applications with a medium heat requirement.

Version:

- Voltage 230 V, 50/60 Hz
- Noise-suppressed
- With support rest
- 1.5-m cable with Schuko plug

Advantage:

- ERS RESTISTRONIC temperature controller for rapid heating up and re-heating using the ceramic PTC heating element
- Lightweight soldering iron without large power transformer, making it ideal for mobile use
- Just as precise as a soldering station thanks to sensitive temperature sensors



Art. no.	54318 020
Type	PTC70
Type description	0832 CDLF
Power rating	75 W
Min./max. temperature conditions	0 to 350 °C
Heat-up time	34 s
Shape of tip	Chisel-shaped
Tip diameter	2.2 mm

EAN-Code

4003008090697