



SIMATIC BusAdapter BA 2xM12, 2 x M12 push-pull sockets, D-coding, also suitable for standard M12

General information	
Product type designation	BA 2x M12
Interfaces	
Number of PROFINET interfaces	1
Supports protocol for PROFINET IO	
<ul style="list-style-type: none"> Number of M12 ports 	2
Cable length	
<ul style="list-style-type: none"> Cu conductors 	100 m
Ambient conditions	
Ambient temperature during operation	
<ul style="list-style-type: none"> horizontal installation, min. horizontal installation, max. vertical installation, min. vertical installation, max. 	-30 °C; No condensation 60 °C -30 °C; No condensation 50 °C
Altitude during operation relating to sea level	
<ul style="list-style-type: none"> Installation altitude above sea level, max. 	5 000 m; restrictions for installation altitudes > 2 000 m, see ET 200SP system manual
Dimensions	
Width	20 mm
Height	73.5 mm
Depth	59 mm
Weights	
Weight, approx.	59 g
last modified:	3/3/2023 