

Datasheet

Art.No. 83.040.1203.0

IP switch WIENET UMS8-4POE-W

wieNET IP Switch, 8 Fast Ethernet ports, of them 4 PoE-Ports, 15,4 W per PoE Port (48 V DC), Ethernet ESD protection, Power line EFT protection. Supports 10/100 Mbps Auto-Negotiation. Broadcast storm protection. Slim line size with DIN-rail/Wall mount and IP30. Metal housing. Redundant 12 ... 48 V DC power input and P-fail-relay. Wide operating temperatures from -40 to 75°C (-40°F ... 167°F)



Art.No.	83.040.1203.0
EAN	4049088370953
Order unit	1 pieces

Approvals

Technical data

Allgemein

Mounting method	DIN rail (top hat rail)
Degree of protection (IP)	IP30
Diagnostic LEDs	P1, P2, P-Fail, 10/100T(x): Link/Activity, Duplex/Collision
Housing material	Metal
Ethernet	Yes
Power over Ethernet	Yes
Fast Ethernet	Yes
Gigabit Ethernet	No
Number of ports 10/100 Mbps RJ45	8
10 Gigabit Ethernet	No
Number of ports 10/100/1000 Mbps RJ45	0
Number of ports 100 Mbps SC	0
Number of 100 Mbps ST-Ports	0

Technical data

Voltage type	DC
Min. operating temperature	-40 °C
Max. operation temperature	75 °C
Redundant power supply	2 power inputs

Supply circuit

Voltage type	DC
Operating voltage min.	24 V
Operating voltage max.	48 V
Power consumption max.	65 W

Dimensions

Depth	95 mm
Width	48.6 mm
Height	140 mm

Classification

ECLASS 8.1	19170106: Network switch
ETIM 5.0	EC000734: Network switch
ETIM 4.0	EC000734: Network switch
ETIM 3.0	EC000734: Network switch

Drawings

