

MILAN S.r.l. a socio unico

Head Office – Export department:

Viale Europa, 74
20090 Cusago (MI) Italy
T. +39 02 9039.4556-4158
F. +39 02 9039.4551
www.taskercables.com

Ufficio Commerciale e Centro Distribuzione

Viale Europa 72 Strada F12
20090 Cusago (MI) Italy
T. +39 02 9039.0037-0059
F. +39 02 9039.0049
www.tasker.it

Technical Datasheet



tasker® C707 U.T.P. CCA Cat. 5e 4x2x0,22 mm² - UL/ETL verified Cable



A	B	C	D
---	---	---	---

ETHERSOUND CATEGORY

Stranded conductors EIA/TIA 568-suitable not only for RJ 45 8 Pin.
Data Transmission Cable (See Audio Catalogue).

- A:** Grey Soft **PVC** Sheath. Outer Cable Diam. Ø 5,00 (±0,10) mm.
B: The four pairs are stranded together with polyester based tape.
C: Insulation with PE – Diam. Ø 0,90 (±0,10) mm.
 RJ45 plug connector compatible.
 Core colors: White – Blue/Blue White-Orange/ Orange, White-Green/Green,
 White-Brown/Brown.
D: Stiff formation of 1x0,50 mm in CCA.
 Nom. Cross section 4x2x0,22 mm².

MARKING CUSTOM

tasker® C707 U.T.P. cat. 5e 4Px24AWG CCA SOLID ISO 1801 100 MHz
 This product is also available in **L.S.Z.H.** polymer, **PE**, **PUR**, with or
 without **Steel Armor**.

Cable Properties

Conductor Resistance	110 Ω/Km ± 5%
Impedance	100 Ω± 5%
Max Rated Voltage	49 V
Operative Temperature	-15/+70°C

USE	<input checked="" type="checkbox"/>	Indoor	Interno Edificio	INSTALLATION	<input checked="" type="checkbox"/>	Fixed	Fissa	INFORMATION	<input checked="" type="checkbox"/>	RoHS2 Compliant
Impiego	<input checked="" type="checkbox"/>	Outdoor Limited	Esterno Limitato	Posa	<input checked="" type="checkbox"/>	Flexible Limited	Flessibilità limitata	Informazioni	<input checked="" type="checkbox"/>	Ver. A / 18.07.2016
		Outdoor Direct Burial	Esterno Interrato		<input checked="" type="checkbox"/>	Dynamic (Drag Chain)	Mobile in Catena			
						Dynamic (Torsion)	Mobile in Torsione			