

Pluggable Terminal Blocks

5 mm Pitch, Standard



FEATURES:

Standard (Latches are on the backside)

Polarised mouldings

Guided pin alignment

Withstand Voltage - AC1500V/1min

SPECIFICATION:

Gender of contacts	Female
Rated current to EN	15 A
Pitch	5 mm
Component type	Wire socket straight
Termination type	Screw Connection
Connection direction	vertical
Rated voltage to EN	250 V
Combustibility class	UL 94 V-0
Colour	green
Temperature range	-33...+120 °C
Cross-section max.	3.3 mm ²
Cross-section min.	0.2 mm ²
Connection cross-section	0.2-3.31 mm ² (24-12AWG)



PRODUCT RANGE:

Art. Nr.	Poles	A	Length
RND 205-00331	2	10 mm	10 mm
RND 205-00332	3	15 mm	15 mm
RND 205-00333	4	20 mm	20 mm
RND 205-00334	5	25 mm	25 mm
RND 205-00335	6	30 mm	30 mm
RND 205-00337	8	40 mm	40 mm
RND 205-00338	9	45 mm	45 mm

