


# EBC003



## Splitter box

ZDO4H050MSS0000-00STAK190MSS



### Application

|                    |  |
|--------------------|--|
| Special feature    | Free from silicone; Gold-plated contacts |
| Free from silicone | yes                                      |

### Electrical data

|                                   |     |   |
|-----------------------------------|-----|---|
| Operating voltage                 | [V] | < 30 AC/DC; ("supply class 2" to cULus) |
| Max. current load per module/slot | [A] | 4                                       |
| Max. current load total           | [A] | 10                                      |

# EBC003



## Splitter box

ZDO4H050MSS0000-00STAK190MSS


| Operating conditions   |  |
|--|--|
| Ambient temperature [°C]   | -25...80                                       |
| Protection   | IP 67; ("enclosure type 1" according to cULus) |
| Mechanical data  |  |
| Weight [g]   | 226.5  |
| Dimensions [mm]  | 33 x 60 x 118.2                                |
| Materials  | PA   |
| Number of ports splitter box   | 4  |
| Connector type   | M12  |
| Accessories  |  |
| Accessories (supplied)   | Protective caps: 2<br>labels: 4                |
| Remarks  |  |
| Pack quantity  | 1 pcs.   |
| Electrical connection - Connection   |  |
| Connector: 1 x M23; Moulded body: PA; Contacts: gold-plated; Tightening torque: 0.8...1.5 Nm |  |
|  |  |



## Splitter box

ZDO4H050MSS0000-00STAK190MSS

### Connection



### Electrical connection - slot

Connector: 4 x M12; Moulded body: PA; Contacts: gold-plated; Tightening torque: 0.8...1.5 Nm

