


SVS ECO VALVE PLUG FORM B 10 MM 230V


2+PE field-wireable M16x1.5

Form B (10 mm)
0...230 V AC/DC, without components
metric

Plastic housings with good resistance against chemicals and oils. The resistance to aggressive media should be individually tested for your application. Further details on request.

[Link to Product](#)**Illustration**

stay connected



Height: 31 mm

Product may differ from Image

Approvals



Form

29765

Technical Data

Operating voltage	0...230 V AC/DC
Operating current per contact	max. 10 A
Connection cross section	0.5...1.5 mm ²
Sealing range (cable diameter)	6...8 mm
Locking of ports	M3 (recommended torque 0.4 Nm)
Contact figure	Cable outlet can be turned in 180° steps
Compression gland	M16 × 1.5 mm
Protection	IP65 inserted and tightened

General data

Temperature range	-40...+80 °C
-------------------	--------------

Commercial data

country of origin	HU
customs tariff number	85369010
minimum order quantity	1