



THOR

SOFT FACED HAMMERS

SPLIT HEAD HAMMERS







These patented Split Head Hammers allow quick changes of faces and handles thereby minimising downtime.

The cast iron heads have two socket head cap screws for uniform distribution of clamping pressure, improving handle and face retention. Extension collars under the head transfer shock to 40% more handle surface, reducing user fatigue and handle breakage. Unique tapered sockets lock faces and handles securely in place, yet the faces can be quickly loosened and rotated for increased service life and uniform wear.

Replacement handles can be locked into the heads without the need for wedges. A significant advantage of this design is the ability to quickly match the hammer's striking face to the task at hand. By choosing either hide, nylon, or super plastic faces, the hammer can be 'customised' to deliver maximum striking power while minimising damage to costly parts.





Hide Hammer	Super Plastic Hammer	Nylon Hammer	Size	Approx Weight 	Face Diameter 		Nominal Length 	Hex Key Size 
					inch	mm		
Ref No.	Ref No.	Ref No.		g	inch	mm	mm	mm
34-RH125	35-SPH125	36-NH125	1	610	1.1/4	32	280	5
34-RH150	35-SPH150	36-NH150	2	900	1.1/2	38	305	6
34-RH175	35-SPH175	36-NH175	3	1450	1.3/4	44	325	6
34-RH200	35-SPH200	36-NH200	4	2000	2	50	350	8
34-RH275	35-SPH275	36-NH275	5	3750	2.3/4	70	400	8
34-RH275FG	35-SPH275FG	-	5L	4200	2.3/4	70	920	8
34-RH400FG	-	-	9	5400	3.1/2	90	920	8
-	35-SPH400FG	-	9	5400	4	100	920	8

FG -Suffix denotes fitted with FibreGlass handle.

SPARE FACES



Size	Face Diameter 		Pack Quantity 	Spare Hide Face	Spare Super Plastic Face	Spare Nylon Face
	inch	mm		Ref No.	Ref No.	Ref No.
1	1.1/4	32	10	70-10R	77-910SPF	76-125NF
2	1.1/2	38	10	70-12R	77-912SPF	76-150NF
3	1.3/4	44	10	70-14R	77-914SPF	76-175NF
4	2	50	10	70-16R	77-916SPF	76-200NF
5 & 5L	2.3/4	70	10	70-22R	77-922SPF	76-275NF
9	3.1/2	90	1	70-400R	-	-
9	4	100	1	-	77-400SPF	-