



AOH(X) & AOH(X) .. G

Generic code	Rubix engineering code	d1	d2	l	a	G	b	g	e	t	Weight (kg)	Dismounting nut	Locknut	Locking device
		(mm)												
AH3040-AKN	890516	190	200	102	6	Tr 215x4	19	-	-	-	3.80	HML43T-AKN	KM38-AKN	MB38-AKN
AH3040G-AKN	891196	190	200	102	6	Tr 210x4	19	-	-	-	3.80	HM42T-AKN	KM38-AKN	MB38-AKN
AH2240-AKN	890485	190	200	118	5	Tr 220x4	19	-	-	-	4.68	HM44T-AKN	KM38-AKN	MB38-AKN
AH24040-AKN	890501	190	200	127	13	Tr 210x4	18	-	-	-	4.00	HM42T-AKN	KM38-AKN	MB38-AKN
AH3140-AKN	890529	190	200	134	6	Tr 220x4	21	-	-	-	5.49	HM44T-AKN	KM38-AKN	MB38-AKN
AOH3140-AKN	891275	190	200	134	6	Tr 220x4	21	M6	5	9	5.55	HM44T-AKN	KM38-AKN	MB38-AKN
AH3240-AKN	891234	190	200	153	7	Tr 220x4	25	-	-	-	6.68	HM44T-AKN	KM38-AKN	MB38-AKN
AH24140-AKN	890511	190	200	158	13	Tr 210x4	18	-	-	-	5.05	HM42T-AKN	KM38-AKN	MB38-AKN
AH2340-AKN	890496	190	200	170	7	Tr 220x4	30	-	-	-	7.54	HM44T-AKN	KM38-AKN	MB38-AKN
AOH2340-AKN	891247	190	200	170	7	Tr 220x4	30	M6	5	9	7.54	HM44T-AKN	KM38-AKN	MB38-AKN
AH3044-AKN	891197	200	220	111	6	Tr 235x4	20	-	-	-	7.40	HML47T-AKN	KM40-AKN	MB40-AKN
AOH3044-AKN	891265	200	220	111	6	Tr 235x4	20	G1/8	8	12	7.40	HML47T-AKN	KM40-AKN	MB40-AKN
AOH3044G-AKN	890595	200	220	111	6	Tr 230x4	20	G1/8	7	12	7.29	HM46T-AKN	KM40-AKN	MB40-AKN
AH2244-AKN	891410	200	220	130	6	Tr 240x4	20	-	-	-	9.10	HM48T-AKN	KM40-AKN	MB40-AKN
AOH2244-AKN	891246	200	220	130	6	Tr 240x4	20	G1/4	9	15	9.10	HM48T-AKN	KM40-AKN	MB40-AKN
AOH24044-AKN	890591	200	220	138	14	Tr 230x4	20	G1/8	7	12	8.20	HM46T-AKN	KM40-AKN	MB40-AKN
AH3144-AKN	890530	200	220	145	6	Tr 240x4	23	-	-	-	10.40	HM48T-AKN	KM40-AKN	MB40-AKN
AOH3144-AKN	890601	200	220	145	6	Tr 240x4	23	G1/4	9	15	10.40	HM48T-AKN	KM40-AKN	MB40-AKN
AOH24144-AKN	891258	200	220	170	14	Tr 230x4	20	G1/8	7	12	10.50	HM46T-AKN	KM40-AKN	MB40-AKN
AH2344-AKN	891172	200	220	181	8	Tr 240x4	30	-	-	-	13.50	HM48T-AKN	KM40-AKN	MB40-AKN
AOH2344-AKN	890589	200	220	181	8	Tr 240x4	30	G1/4	9	15	13.50	HM48T-AKN	KM40-AKN	MB40-AKN
AH3048-AKN	890517	220	240	116	7	Tr 260x4	21	-	-	-	8.75	HM52T-AKN	HM44T-AKN	MB44-AKN
AOH3048-AKN	890596	220	240	116	7	Tr 260x4	21	G1/4	9	15	8.75	HM52T-AKN	HM44T-AKN	MB44-AKN
AOH24048-AKN	890592	220	240	138	15	Tr 250x4	20	G1/8	7	12	9.29	HM50T-AKN	HM44T-AKN	MB44-AKN