



## PREMIUM CORDED UC HEADSET

### **BENEFITS**

- Block disruptions from close talkers and environmental noise with the flexible, noise-canceling microphone enhanced with Acoustic Fence technology
- Optimize audio comfort and quality with advanced hybrid active noise canceling (ANC) by choosing between three settings
- Prevent interruptions by others with the on-call indicator that lets others know when you're on a call
- Audio is always exceptional for both calls and media with enhanced bass response

### **BLACKWIRE 8225**

Is background noise affecting productivity? Help teams keep noise out and focus—with the Poly Blackwire 8225 premium headset. Conversations stay clear and private with the flexible, noise-canceling microphone enhanced with Acoustic Fence technology. And users have less distractions with the built in on-call indicator. Users can customize their experience by adjusting the hybrid active noise canceling (ANC) to suit their environment. So sound quality for calls and stereo music is premium. And the fit is, too—lightweight and comfortable, designed for wearing all day.

- Flexible, noise-canceling microphone with Acoustic Fence technology
- Advanced hybrid active noise canceling (ANC) with three settings to optimize
- Lightweight design (.41 lbs/186 g)
- Fully adjustable headset with 180° pivoting speakers
- Choose the variant for your device, USB-A or USB-C
- Microsoft Teams version with dedicated Teams button for instant access

# BLACKWIRE 8225



## SPECIFICATIONS

### CONNECTS TO

- PC/Desk phone via USB-A/USB-C

### COMPATIBLE WITH

- Windows® or Mac OS

### PC AUDIO RECEIVE FREQUENCY RESPONSE

- Dynamic EQ optimized for PC wideband voice telephony up to 7 kHz or for multimedia 20 Hz to 20 kHz

### SPEAKER SENSITIVITY

- 84 dB SPL (1 mW/1 cm) +/- 3 dB

### SPEAKER IMPEDANCE

- 32 Ohm

### SPEAKER SIZE

- 32 mm

### ANC TECHNOLOGY

- Advanced Hybrid ANC using four digital microphones with three user selectable options

### MICROPHONE AND TECHNOLOGY

- Noise canceling with Acoustic Fence technology (using two microphones) to Microsoft Teams Open Office-certification levels

### MICROPHONE FREQUENCY RESPONSE

- 100 Hz to 10 kHz optimized for PC wideband audio up to 7 kHz

### MICROPHONE SENSITIVITY

- -35 dBV/Pa ± 3 dB

### HEARING PROTECTION

- SoundGuard DIGITAL: Acoustic limiting for protection against sounds above 118 dBA. G616 anti-startle protection limits the noise level to 102 dB SPL; Time-Weighted Average prevents average daily noise exposure from exceeding 80 or 85 dBA (enabled by Plantronics Hub software)

### WEIGHT

- .41 lbs/186 g

### CALL CONTROLS

- BW8225: Call answer/end, mute, volume: up and down, ANC: off, mid and high
- BW8225-M: Call answer/end (Microsoft Teams button), mute, volume: up and down, ANC: off, mid and high

### ONLINE INDICATOR

- Two LED indicators on speaker housing show online/in a call status

### VOICE ALERTS

- Volume maximum, volume minimum, mute on, mute off, noise canceling off, answering call

### CABLE LENGTH

- 7.2 ft/2.2 m

### APPLICATIONS SUPPORTED

- Plantronics Hub desktop version only, available for Windows/Mac. Plantronics Manager Pro suites: Asset Management and Adoption, Call Quality and Analytics, Health and Safety

## LEARN MORE

For more information on Blackwire 8225 visit [poly.com/Blackwire-8225](https://poly.com/Blackwire-8225)