

## Liquid-Tight, Strain Relief Cordgrips *1427CG Series*

### Features



- Black nylon, liquid-tight cordgrip.
- Used where cable is entering or leaving an enclosure.
- Accepts a wide range of cable diameters due to large opening and highly flexible strain relief elements, together with a TPE sealing ring.
- The strain relief elements tighten in a circular sequence on the sealing ring to give outstanding strain relief without twisting or damaging the cable.
- Use the cordgrip with the smallest maximum diameter that will fit your application (see table below).
- Nylon locknut included (as shown).
- Suitable for NEMA type 4 applications - Protection to IP68.
- UL94-V2 flammability rating.
- UL, CSA & VDE listed.

Part No.	Use With Wire Diameter		Mounting Hole
	Min	Max	Diameter
<b>1427CG7</b>	0.10	0.26	0.49
<b>1427CG9</b>	0.14	0.32	0.60
<b>1427CG13</b>	0.24	0.47	0.80
<b>1427CG16</b>	0.35	0.55	0.89
<b>1427CG21</b>	0.51	0.71	1.11

*Data subject to change without notice*