

PRODUCT-DETAILS

# FLT0430

## LT-T FLEXIBLE CONDUIT 20MM



### General Information

Extended Product Type	FLT0430
Product ID	7TCA297020R0182
EAN	5011949214859
Catalog Description	LT-T FLEXIBLE CONDUIT 20MM
Long Description	Liquid Tight, Low Fire Hazard Conduit, Nominal Conduit Size 20mm, 1/2 Inch US Trade Size, Outside Diameter 21.1mm, Inside Diameter 15.9mm, Static Bend Radius 80mm, Reel Length 30 Meters, Galvanised Steel Core, String Packing with LFH Covering, Black

### Ordering

EAN	5011949214859
Customs Tariff Number	8307106000

### Dimensions

Product Net Weight	25.9 lb 11.746 kg
--------------------	----------------------

### Container Information

Package Level 2 Units	1 piece
Package Level 2 Width	1 in 25 mm

Package Level 2 Height	1 in 25 mm
Package Level 2 Depth / Length	1 in 25 mm

### Additional Information

Application	Indoors / Outdoors, Marine, Buildings, & Rail Infrastructure Where Low Smoke and Toxicity are of Concern
Brand / Label	Kopex
Color	Black
Flexibility	Medium
Inside Diameter	15.9 mm
Material	Galvanized Steel Core with String Packing and Low Fire Hazard Coating
Nominal Size	1/2 in NC20
Number of Batteries	0
Outside Diameter	21.1 mm
Product Name	flex metal conduit
Product Type	Liquid Tight Low Fire Hazard Conduit
Radius	80 mm
Standards	BSI Kitemark KM-90009, Low Voltage Directive, London Underground I-085, NFF16-101 (I1 F1)
UPC	786210276809

### Certificates and Declarations (Document Number)

Data Sheet, Technical Information	FLT0430
Declaration of Conformity - CE	9AKK107492A9617
Instructions and Manuals	FLT0430

### Classifications

ETIM 6	EC001179 - Protective metallic hose
ETIM 7	EC001179 - Protective metallic hose
UNSPSC	39131706
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5543 >> Liquid Tight Conduit

### Categories

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Flexible Cable Protection Systems

