

EMITLIGHT IR ILLUMINATORS

IR-POE SERIES



TECHNICAL SPECIFICATION

Maximum illumination distance	98 m (depends on the illumination angle)
Supply voltage:	11 – 30 VDC
Power consumption:	12 W
Wavelength:	858 nm / 932- 940 nm
Weight	1100 g
Operating temperature	from -40°C to +60°C (from -40°F to 140°F)
IP protection level	IP67
Illumination angle	15°/ 30°/ 45°/ 60°/ 90°/120°
Colours	Anodized black/white/anodized silver/anodized gold
Digital input for the activation of the illuminator	Yes
Automatic activation with the help of photoswitch	No
Illumination level of automatic activation	≤ 6 lux
Delay of the deactivation	150 s
Source of light	4 pcs. High Power SMD LED
Length of supply cable:	0,7m (27,56 inches)
Dimensions:	
width	115 mm (4,53 inches)
height	90 mm (3,54 inches)
thickness	51 mm (2,01 inches)