

TDMX cutting body MS (M)



Application:

First choice for stainless steel and heat-resistant alloy applications

Execution:

- Precision-ground indexable insert, tip angle 140°

Art. no.	11225 209
Brand	WIDIA
Manufacturer Part Number	6568981
Cutting edge diameter	20.9 mm
Indexable insert type	E
Carbide type	WM15PD
Surface	TiAlN
Cutting material	SC
Angle of the tip	140 Degree
Gross Weight	0.065 kg
Product Group	1XA

