

META COMPACT single-sided office boltless rack



Application:

Clearly arranged storage of binders. Ideal for archives and offices.

Execution:

- zinc-plated, with disassembled frame or coated in light grey RAL 7035, with clinched/ pre-assembled frame
- quick boltless assembly without tools
- Add-on rack, for expanding the basic rack
- Shelves complete with end stop (optional cover shelf without end stop)
- Shelves/profiles made of high-quality steel, shelves adjustable in increments of 25 mm
- with steel feet suitable for anchoring
- Shelf height is more than 5 times the shelf width!
- Basic rack planning dimensions: Nominal length + 56 mm, nominal depth + 36 mm add-on rack planning dimensions: Nominal length + 6 mm, nominal depth + 36 mm



Art. no.	50166 227
Brand	META
Manufacturer Part Number	20083160
Height	2200 mm
Length	756 mm
Depth	336 mm
Nominal length	750 mm
Nominal depth	300 mm
Type of shelving	Add-on shelving
Design	One side
Type of assembly	To insert
Surface	Plastic-coated
ESD-capable	No
Design of the frame	Pre-assembled
Grid dimension	25 mm
Number of shelves	6 PCS
Load-carrying capacity per shelf	80 kg
Number of frame	1 PCS
Quality label	RAL-RG 614/1
Made in	Germany
Product certification	Institute for Materials Research and Testing (MPA) North Rine Westphalia (NRW) (Dortmund)
Approval mark	GS certified safety
Approval mark - Product certification	GS certified safety - Institute for Materials Research and Testing (MPA) North Rine Westphalia (NRW) (Dortmund)
Gross Weight	19.080 kg
Product Group	508

EAN

4026212153637