

Power 180-5 W OF air compressor

metabo[®]

Version:

- For single-phase alternating current
- Oil-free piston compressor
- Pressure reducer with manometer for controllable working pressure
- Instrument panel with easily legible manometers for tank and operating pressure
- Cord wrap facility

Advantage:

- Push button with starter valve for reliable cold start
- Reduced service costs

Delivery:

Universal quick-release coupling



Art. no.	75290 100
Model	Power 180-5 W OF
Operating pressure	8 bar
Intake air capacity	160 l/min
Delivery quantity effective at 80% max. pressure	75 l/min
Filling capacity	90 l/min
Tank capacity	5 l
Power input	1.1 kW
Max. rotation speed	2850 rpm
Length x width x height	370 x 395 x 286 mm
Weight	16 kg
With overload protection	Yes

EAN-Code

4007430244406