

## PAR64 64737/4 VNSP

PAR64 | Halogen lamps with parabolic reflector PAR64, with pin base



### Areas of application

- Events
- Performances
- Stage productions

### Product family benefits

- Easy lamp replacement
- Flexible operating position

### Product family features

- The parabolic glass reflector and the front lens are fused together
- High luminous intensity
- Available in different beam angles to ensure high flexibility



# Product datasheet

## Technical data

### Electrical data

Nominal voltage	240 V
-----------------	-------


### Photometrical data

Color temperature	3200 K
Luminous intensity	320000 cd

### Light technical data

Beam spot height	43 m
------------------	------

### Dimensions & weight



Light center length (LCL)	102.0 mm
Length	152.4 mm
Diameter	204.0 mm

### Lifespan

Lifespan	300 h
----------	-------

### Additional product data

Base (standard designation)	GX16d
-----------------------------	-------

### Capabilities

Burning position	Other <sup>1)</sup>
------------------	---------------------

<sup>1)</sup> Do not tilt perpendicular to the filament

### Country specific categorizations

ANSI code	Other
-----------	-------

Environmental information

Information according Art. 33 of EU Regulation (EC) 1907/2006 (REACH)	
Date of Declaration	17-04-2023
Primary Article Identifier	4008321644039   4062172359214
Declaration No. in SCIP database	In work

## Product datasheet

---

### Safety advice

To prevent personal injury or damage to property, halogen lamps may only be operated in suitable luminaires designed with suitable mechanisms (cover panel etc.) to ensure that in the event of a lamp bursting no parts/shards can escape and that during operation no ultraviolet radiation can escape. Because of the heat produced only heat-resistant lamp connections (holders) may be used. Do not operate near people, or any materials that are flammable, sensitive to heat or affected by drying out. Detailed information is available on request.

---

### Logistical Data

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Volume	Gross weight
4062172359214	PAR64 64737/4 VNSP	Folding carton box 1	179 mm x 179 mm x 204 mm	6.54 dm <sup>3</sup>	1069.00 g
4062172359221	PAR64 64737/4 VNSP	Shipping carton box 6	594 mm x 411 mm x 265 mm	64.70 dm <sup>3</sup>	7454.00 g

---

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

---

### Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.

---