




The head marking is determining



**BN 4851**

**Hexalobular (6 Lobe) socket flat countersunk head screws**


fully threaded


Steel 08.8 / 8.8

zinc plated blue

**i** Fasteners to the given specification have a reduced loadability due to the head geometry according to ISO 898-1.

Article#	d <sub>1</sub>	d <sub>2</sub> max.	k max.		t max.	A~	L
3645853	M2	3,8	1,2	X6	0,64	1,75	3
3271456							4
3271457							5
3271458							6
3271460							8
3271462							10
3271463							12
3271464							16
3645854	M2,5	4,7	1,5	X8	0,79	2,4	3
3271465							4
3271466							5
3271467							6
3271468							8
3271469							10
3271470							12
3271471							16
3645855							20
3645857	M3	5,5	1,65	X10	0,83	2,8	4
3271472							5
1146262							6
1146270							8
1148494							10
1148508							12
1148516							16
3055853							20
3271473							25

Article#	d <sub>1</sub>	d <sub>2</sub> max.	k max.		t max.	A~	L
3271474	M3	5,5	1,65	X10	0,83	2,8	30
3645858							35
3645859							40
3645860	M4	8,4	2,7	X20	1,53	3,95	5
1148524							6
1148532							8
1148540							10
1148559							12
1148567							16
1148575							20
3055854							25
3271475							30
3271476							35
3271477							40
3645861							45
3645862							50
3645863	M5	9,3	2,7	X25	1,51	4,5	6
1148583							8
1148591							10
1148605							12
1148613							16
1148621							20
3055855							25
3271478							30
3271479							35
3271480							40
3645864							45
3645865							50
3271481	M6	11,3	3,3	X30	1,78	5,6	8
1148648							10
1148656							12
1148664							16
1148672							20
1148680							25
3055856							30
3271482							35
3271483							40
3271484							45
3271485							50
3645866							55
3645868							60

Article#	d <sub>1</sub>	d <sub>2</sub> max.	k max.		t max.	A~	L
3271486	M8	15,8	4,65	X45	2,54	7,95	10
3070468							12
3070470							16
3070472							20
3070473							25
3070475							30
3271487							35
3271488							40
3271489							45
3271490							50