

TECHNICAL SPECIFICATIONS

D-Sub Hood:


Material: UL 94 V-0 Plastic Material
 Plating: Nickel over Copper
 Operating Temperature: -55°C to +110°C
 Cable Entry: Side Entry
 Thumbscrews: UNC 4-40 (Standard)
 Cable O.D: Up to 11,5mm

D-Sub High Density:

Insulator: PBT, Black, UL94 V-0
 Shell: Stamped Steel, Tin Plated
 Contact pins: Copper Alloy
 Stamped & Formed pins: 100 inserts min
 Contacts Plating: Selective Gold over Nickel
 Operating Temperature: -55°C to +105°C
 Withstanding voltage: 500V for 1 minute
 Insulator resistance: 500MΩ min


Features:

- Available in sizes 9-15-25-37
- Suitable for any common Sub-D Connector
- Strain relief inserts ensure a secure termination
- Re-openable
- Recyclable



D-Sub-Hood

Grommet Sizes D45PK-M:



Size D45PK-M	Dim A	Dim B	Dim C
9-way	31,0	36,3	15,0
15-way	39,5	40,3	15,0
25-way	53,2	40,3	15,0
37-way	69,7	40,3	15,0

Ordering information:

D-Sub Connector Kits (100 inserts min.)

Size:	P/N - Kitted:	Product Code - MALE Conn. Kit
15-way	6355-0057-01	D45PK-M-09-HDP15-K
26-way	6355-0057-02	D45PK-M-15-HDP26-K
44-way	6355-0057-03	D45PK-M-25-HDP44-K
62-way	6355-0057-04	D45PK-M-37-HDP62-K

Size:	P/N - Kitted:	Product Code - FEMALE Conn. Kit
15-way	6355-0057-11	D45PK-M-09-HDS15-K
26-way	6355-0057-12	D45PK-M-15-HDS26-K
44-way	6355-0057-13	D45PK-M-25-HDS44-K
62-way	6355-0057-14	D45PK-M-37-HDS62-K