



Backlight Panel

BACKLIGHT UGR19 36W 30X120 4K

Order code **70087**

EAN **8002219870094**

Technical specifications


Absorbed Power	36 W
Supply voltage type	AC
Nominal voltage (AC)	230 Vac
Ambient temperature (min)	-20 °C
Ambient temperature (max)	40 °C
Insulation class	II
CCT light tone	4000 K
Optical protection grade	IP40
Photobiological risk	RG0
Colour consistency	SDCM3
Colour trim	White
CRI color rendering	>80
Driver type	ED
Efficiency	100 lm/W
Equivalent power	2x36w
Frequency (max)	60 Hz
Frequency (min)	50 Hz
Power factor	0.95
Glow wire strength	650 °C - 30s.
Inrush current	27 A
Inrush time	0.15
Luminaire flux	3600 lm
Luminous flux L80B20	30000 h
Breaker B10 (Qty max)	20
Breaker B16 (Qty max)	33
Breaker C10 (Qty max)	34
Breaker C16 (Qty max)	56
THD	20
UGR	19
Voltage supply range (max)	253 V
Voltage supply range (min)	207 V

Installation and applications

Environment	Offices
Application	Offices, Shops

Mechanical specifications

Height	34 mm
Length	1195 mm
Width	295 mm



Weight	2.4 Kg
Body material	White Lacquered Aluminium
Colour housing	White
Cover material	PMMA transparent thermoplastic
Box protection grade	IP20
Protection grade IP	IP20/IP40
Protection grade IK	IK05

Certifications and norms

UK SI 2021 No. 1095, EN IEC 55015:2019 + A11:2020, EN IEC 61000-3-2 :2019, EN 61547:2009, EN 62471:2008, EN IEC 60598-1:2021, EN 60598-2-2:2012, EN IEC 63000:2018, EN 62493:2010, EN 61000-3-3:2013


Accessories



19359
INV P&L LED SE/SA 3H 20-60V



70033
SUSPENSION WIRE PANELED



20101
CORNICE PLAF BACKLITE
300X1200



19358
INV P&L LED SE/SA 1H 20-60V



70049
CLIPS UNIVERSALE CGRESSO
M600