


**CUBE20S POWER MODULE**

24VDC

Power module  
Expansion module  
for external voltage supply

[Link to Product](#)**Illustration**

Product may differ from Image

**Approvals**



### General data

Protection	IP20
Connection	Spring clamp terminals: 0.08...2.5 mm <sup>2</sup> (AWG 28...12)
Mounting method	DIN-rail mountable (EN 60715)
Temperature range	0...+60 °C (storage temperature -25...+70 °C)
Dimensions H × W × D	109×12.9×76.5 mm

### Output

Output current (I/Os /Backplane)	10/0 A
Output voltage (I/Os /Backplane)	24 V AC

### Module Supply

Operating voltage	max. 28.8 V DC
Total current	max. 10 A

### Commercial data

country of origin	TH
customs tariff number	85369010
minimum order quantity	1