




90 series adjustable wrench

90

MORE DETAILS ABOUT PRODUCT

- Adjustable wrenches developed according to the scientific ERGO™ process
- Standards: ISO 6787, DIN 3117, ASME B107.8M - 1996 and BS 6333
- High performance alloy steel
- Comfortable non-slip thermoplastic grip handle
- Scale in mm for pre-adjusting and accurate measurement
- The jaw does not fall out even at maximum opening of the wrench
- Head angle 15° provides better accessibility
- Left turning screw
- P series: Reversible jaw for pipe use
- Black finish. Precision hardened and anti-corrosion treated



Product	A	Total length_in_A.eps_Metric	B	C	D	Jaw height_mm_E.eps_Metric	 g
9070	158 mm	6 in	20 mm	5,3 mm	11,3 mm	19 mm	139 g
9070 P	158 mm	6 in	21 mm	5,3 mm	11,3 mm	19 mm	139 g
9071	208 mm	8 in	27 mm	6 mm	12,9 mm	24 mm	272 g
9071 P	208 mm	8 in	28 mm	6 mm	12,9 mm	24 mm	272 g
9072	257 mm	10 in	31 mm	8,7 mm	15,5 mm	29 mm	425 g
9072 P	257 mm	10 in	33 mm	8,7 mm	15,5 mm	29 mm	430 g
9073	308 mm	12 in	34 mm	11,9 mm	17,6 mm	34 mm	730 g
9073 P	308 mm	12 in	35 mm	11,9 mm	17,6 mm	34 mm	745 g