


Series MXQ

Dimensions: MXQ12

Basic style

* For detailed dimensions about the stroke adjuster, refer to the option for the stroke adjuster.
 Rubber stopper (Refer to page 122.)
 Metal stopper (Refer to page 125.)



| Model | F | N | G | H | NN | GA | HA | I | J | K | KA | NA | M | Z | ZZ |
|-----------|----|----|-------|-------|----|----|----|----|-----|-------|-------|----|-----|-----|-----|
| MXQ12- 10 | 28 | 4 | 18 | 32 | 2 | 18 | 32 | 12 | 34 | 26.5 | — | 4 | 67 | 66 | 76 |
| MXQ12- 20 | 28 | 4 | 18 | 32 | 2 | 18 | 32 | 12 | 34 | 36.5 | — | 4 | 67 | 66 | 76 |
| MXQ12- 30 | 38 | 4 | 20 | 40 | 2 | 20 | 40 | 14 | 42 | 46.5 | — | 4 | 77 | 76 | 86 |
| MXQ12- 40 | 34 | 6 | Note) | Note) | 3 | 38 | 39 | 15 | 58 | 56.5 | — | 4 | 94 | 93 | 103 |
| MXQ12- 50 | 34 | 6 | 9 | 39 | 3 | 48 | 39 | 13 | 70 | 66.5 | — | 4 | 104 | 103 | 113 |
| MXQ12- 75 | 36 | 8 | 23 | 36 | 4 | 59 | 72 | 17 | 110 | 91.5 | 117.5 | 8 | 148 | 147 | 157 |
| MXQ12-100 | 36 | 10 | 12 | 36 | 5 | 84 | 72 | 17 | 135 | 116.5 | 142.5 | 8 | 173 | 172 | 182 |

Note) Refer to the bottom view of MXQ12-40.