


WIRE ADDRESS



- Electrical Test:
- 1.100% TEST OPEN SHORT MIS-WIRE.
 - 2.CONTACT RESISTANCE:3Ω MAX.
 - 3.INSULATION RESISTANCE:5MΩ MIN.
 - 4.HI-POT:300V DC/10MS.
 - 5.SUPPORT USB 2.0 480Mbps

E		F	BLACK TPE(65A)		G
E		E	USB Micro BSP Aluminum shell(Gold)	1	PCS
D		D	USB AM Aluminum shell(Gold)	1	PCS
C		C	MICRO USB 5P BM Reversible type (Gold plated)	1	PCS
B		B	USB AM(White Insulator,Gold Plated)	1	PCS
A		A	NON-UL 28#*1P+20#*2C+AL,BLACK TPE JACKET+BLACK COTTON BRAID(CONTAIN GOLD RIBBON),OD:4.2mm	1	PCS
F		PRODUCT SPECIFICATIONS			
NUMBER		1	2	4	

D		GOLD USB 2.0 Cable, A - Micro B (reversible), M/M, 1.8 m		VER.A	REVISE	DATE
C						
B						
Item		11.02.8820				
Draw		*Note		Date: 2018.11.16		
Approval						
Duty		F16		BOM.NO:		
Sample NO.				Drawings of 1 (1)		
				Proportion: 1:1		
				Unit(mm)		
				A4		

