



Datenblatt - Fiche technique - Data sheet


**19.08.1022**



ROLINE Y-Netzanschlusskabel, 2,0m

ROLINE Câble d'alimentation en Y, 2,0m

ROLINE Y-Power Cable, 2x straight IEC Connector, 2 m



No	BOM ITEM	Q' TY	P/N
1	SP-023 INSERT	1 PCS	MB023012
2	PVC 50P (SP-023)	41 g	RPP05012
3	KPR-14 TERMINAL	6 pcs	BBB14000
4	IS-14 INNER BODY	2 pcs	MI014000
5	PVC 50P (IS-14)	37.7 g	RPP05012
6	T type SR INNER BODY	1 PCS	MI01Y012
7	J631-BS-0	3 PCS	BEB31BS0
8	PVC 50P (SY-01)	38 g	RPP05012
9	PE TIE (BLACK , 7inch)	1 pcs	KBBPE118
10	PE BAG	1 pcs	KPR12277
11	LABEL	1 pcs	KLL27617
12	PE LABEL	1 pcs	KLL27779
13	H05VV-F 3G 0.75(500mm*2)	2 pcs	

E: Yellow/Green  
 N: Blue  
 L: Brown

線材印字: (四字)

I-SHENG KSIS ◁VDE▷ KEMA-KEUR 1353 IEMMEQU H05VV-F 3G 1.0mm<sup>2</sup> 60227 IEC 53 RVV 300/500V A041481 3ASL/100 4V-75 V-75(75°C) 250/440V ORDINARY DUTY Q90033 -LF- CE

I-SHENG KSIS ◁VDE▷ KEMA-KEUR 1353 IEMMEQU H05VV-F 3G 0.75mm<sup>2</sup> 60227 IEC 53 RVV 300/500V A041481 3ASL/75 4V-75 V-75(75°C) 250/440V ORDINARY DUTY Q88228 -LF- CE

CABLE	H05VV-F 3G 1.0 3ASL/100 RVV 300/500V CT-12 (BLACK)			
PLUG	SP-023 + IS-14+IS-14	LENGTH	2000	UNIT mm
P/N	19.08.1022	KS DWG	SR-1502176	VER. A

**rotronic**