

811.1019

**M** Screwdriver and hook set



568 x 398

P10

P10TC

P15

P20


P30

P35

P45



Pos.	Code	Description	pcs
1	159.1128	EERGOTORQUEplus screwdriver for phillips screws PH, extra long, PH2, 405 mm	1
2	159.1107	ERGOTORQUEplus screwdriver for slotted screws, extra long, 5,5 mm, 405 mm	1
3	550.1047	Hook, 45° offset	1
4	550.1049	Hook, 135° bent	1
5	550.1046	Hook, straight	1
6	550.1048	Hook, 90° offset	1
7	550.1075	T hook, S form large, 165 mm	1
8	550.1074	T hook, S form small, 120 mm	1
9	151.1133	ERGOTORQUEmax hammer cap screwdriver slotted, 8 mm	1
10	151.1132	ERGOTORQUEmax hammer cap screwdriver slotted, 7 mm	1
11	151.1128	ERGOTORQUEmax hammer cap screwdriver slotted, 5,5 mm	1
12	151.1104	ERGOTORQUEmax hammer cap screwdriver, PH2, 185 mm	1
13	151.1102	ERGOTORQUEmax hammer cap screwdriver, PH1	1
14	140.2615	Clip remover short, length 240 mm, opening 9 mm	1
15	550.1071	Hook, large, straight	1
16	550.1072	Hook, large, 90° bent	1
17	550.1073	Hook, large, sickle	1
18	911.8101	Pry bar, 11 x 115 mm	1
19	911.8102	Pry bar, 15 x 185 mm	1



P 10

P 15

P 20

P 25

P 30

P 35

P 40

P 45

M

S

XL

L

Individual parts

Accessories