




Part Number : MPSB 130/30
Proximity Switch - Reed Switch based
Rectangular - Normally Closed Contacts - Suggested Magnet: MPSM
Product Data Sheet


PICTURE	DIMENSIONS	Applications Include
	 <p>Drawings not to scale All dimensions in mm(inches) nominal</p>	<ul style="list-style-type: none"> ● Position and limit sensing. ● Linear actuators . ● Security system switch. ● Door Switch.
Options		<ul style="list-style-type: none"> ● Also available in all Black. ● White economy version available. ● Left and Right hand version available. ● Custom cable lengths, strip lengths, cable types, terminations. ● If you do not see what you need, just ask, as there is a strong possibility we can do it !


✓RoHS Compliant


SPECIFICATION	
Contact Form / Style	Normally Closed
Switching Capacity (Resistive)	5 W/VA Max.
Switching Voltage	100 VAC Max.
Switching Current	0.5 A. Max.
Carry Current	1.0 A. Max.
Breakdown Voltage	200 VDC Min.
Contact Resistance	150 mOhms Max.
Switching Distance	8 mm Min.
Operating Temperature Range	-40°C +105°C
Storage temperature	-25°C +90°C
Case Material	Glass Filled Nylon
Cable	2 x Round 0.25mm ² Irradiated PVC insulated Grey


Did you know we also sell?



Float Switches



Magnets


Movement Sensors


Tilt / Tip Switches


Acceleration / Shock Switches


Reed Relays


Solid State Relays

Rev. No.	Revision Note	Date	Signature
3	Datasheet Redesign	14-02-11	ML