

HARTING Cabinet Outlet RJ45, 8-poles
 RJ45 distribution module for IP20 environments
 (top-hat rail mounting)



Advantages

- Simple mounting
- Dust protection caps
- Port identification
- Angled output

Technical characteristics

Number of ports, Copper / Termination	1 / RJ45 (Twisted Pair)
Transmission performance	Category 6A / Class E _A up to 250 MHz acc. to ISO/IEC 11 801:2002, EN 50 173-1
Transmission rate	10/100 Mbit/s and 1/10 Gbit/s
Mounting	To 35 mm top-hat mounting rail acc. to DIN EN 60 715, alignable
Dimensions (H x W x D)	71 x 18 x 68 mm
Degree of protection	IP20
Operating temperature range	-20 °C ... +70 °C
Housing material	Polyamide, UL94 V-0
Colour	Grey

Identification	Part No.	Drawing	Dimensions in mm
----------------	----------	---------	------------------

HARTING RJ Industrial®
 Cabinet Outlet RJ45

09 45 851 0000

Protection cover set
 for 09 45 851 0000

09 45 851 0001

Usable RJ45 cable jacks

- Ha-VIS preLink® keystone set AWG 22/23 (with Ha-VIS preLink® terminal block)
- Ha-VIS preLink® keystone set (without Ha-VIS preLink® terminal block)

20 82 501 0001

20 82 500 0001

Usable with Ha-VIS preLink® terminal blocks

- Ha-VIS preLink® terminal block AWG 22/23 (24)
- Ha-VIS preLink® terminal block AWG 26/27

20 82 000 0001

20 82 500 0003

Usable RJ45 cable jacks

- RJ45 keystone module IDC AWG 24 – AWG 22
- RJ45 keystone module IDC AWG 27 – AWG 26

09 45 545 1564

09 45 545 1563

