

SKINTOP® accessories metric

Halogen-free counter nut



SKINTOP® GMP-HF-M

Application

The halogen-free counter nuts with metric thread are adapted in quality and workmanship to our metric SKINTOP® cable glands. For universal use if personal and property protection is a priority:

- Offices
- Public buildings
- Underground railways
- Tunnel construction
- Ventilation systems

- Industrial plants
- Warehouses
- Building services
- Ship and boat building

Advantage

- Hexagonal counter nut
- Metric thread
- Extremely flame-retardant
- Halogen-free
- Self-extinguishing, no dripping

Note

- Designed for use in connection with SKINTOP® ST-HF-M



Technical Data



Note
Dimension sheet available on request



Colour delivered
RAL 7035 light grey



Material
Polyamide UL94 V0 - halogen free



Range of temperature
-20°C up to +100°C

Part number	Part designation / size	Width across flats mm	PU pieces
SKINTOP® GMP-HF-M			
53119200	12 x 1.5	17	100
53119210	16 x 1.5	22	100
53119220	20 x 1.5	27	100
53119230	25 x 1.5	34	100
53119240	32 x 1.5	41	100

SKINTOP® ST-HF-M

Halogen-free cable gland in accordance with EN 50262 for fast assembly



SKINTOP® ST-HF-M Completely halogen-free

Application


The easy-to-assemble metric cable gland with the proven properties of the internationally well-known SKINTOP® glands. SKINTOP® ST-HF-M is suitable for universal use when personal and property protection is a priority.

- Offices
- Public buildings
- Underground railways

- Tunnel construction
- Ventilation systems
- Industrial plants
- Warehouses
- Building services
- Ship and boat building

Advantage

- Maximum reliability
- Metric thread
- Extremely flame-retardant
- Completely halogen-free
- Self-extinguishing, no dripping
- Permanent vibration protection



Technical Data

⚠ Caution
Installation dimensions and
tightening torques
see T21

📄 Approvals
VDE / EN 50262
Filament wire test
EN 60695-2-1/1
+960°C

🎨 Colour delivered
RAL 7035 light grey

🛡 Degree of protection
IP 68

🏠 Material
Polyamide UL94 V0 - halogen free
Seal: LSE 1 - halogen free
O-ring: LSE 1 - halogen free

🌡 Range of temperature
-20°C up to +100°C

Part number	Part designation / size	Clamping range F mm	SW mm	C mm	D mm	PU pieces
SKINTOP® ST-HF-M						
53111407	ST-HF-M 12 x 1.5	4 - 5,5	15	30	8	100
53111417	ST-HF-M 16 x 1.5	4,5 - 9	19	34	8	100
53111427	ST-HF-M 20 x 1.5	7 - 13	25	37	9	100
53111437	ST-HF-M 25 x 1.5	9 - 17	30	40	10	50
53111447	ST-HF-M 32 x 1.5	11 - 21	36	47	10	25