









OPTOTRONIC® LED Power Supply

1) **OPTOTRONIC® INTELLIGENT OTi DALI 80/220-240/1A6 LT2 L**        

Constant current LED Power Supply

I_{out} [mA]	U_{in} [V]	U_{out} [V]	U_{out} [V]	I_{out} [mA]	λ	λ [°C]
600-1850	80	20-54	220-240V 0/240/0V	0.41	0.95	-45...90

OSRAM GmbH
Dorfstr. 16
93041 Regensburg
Germany
www.osram.com

IS 15885
(Part 2, Sec 13)
R4 125515
www.bis.gov.tr

Connect PE to case of PFI 4
www.osram.com
www.ledset.com
R4 125515
www.bis.gov.tr

Designed and engineered in Italy
Made in Bulgaria by OSRAM

LED+ \bullet 21, \bullet 22
LED- \bullet 23, \bullet 24
LEDset \bullet 25
LED-aux \bullet 26, \bullet 27

$t_c = 80^\circ\text{C}$

SELV

OTi DALI 80/220-240/1A6 LT2 L

picture only for reference, valid print on product 10)

1) **OPTOTRONIC® INTELLIGENT OTi DALI 80/220-240/2A1 LT2 L**        

Constant current LED Power Supply

I_{out} [mA]	U_{in} [V]	U_{out} [V]	U_{out} [V]	I_{out} [mA]	λ	λ [°C]
1000-2100	80	20-54	220-240V 0/240/0V	0.41	0.95	-45...90

OSRAM GmbH
Dorfstr. 16
93041 Regensburg
Germany
www.osram.com

IS 15885
(Part 2, Sec 13)
R4 125515
www.bis.gov.tr

Connect PE to case of PFI 4
www.osram.com
www.ledset.com
R4 125515
www.bis.gov.tr

Designed and engineered in Italy
Made in Bulgaria by OSRAM

LED+ \bullet 21, \bullet 22
LED- \bullet 23, \bullet 24
LEDset \bullet 25
LED-aux \bullet 26, \bullet 27

$t_c = 80^\circ\text{C}$

SELV

OTi DALI 80/220-240/2A1 LT2 L

picture only for reference, valid print on product 10)

A

Input⁶⁾ Output⁷⁾ **SELV**

1-Mains⁵⁾ 2-Mains 3-n/a 4-PE 5-n/a 6-DALI 7-DALI

Touch DIM

PE DA DA

LED+ LED- LEDset LED-aux

SEC U-OUT = 60V


21-LED+ 22-LED- 23-LED+ 24-LED- 25-n/a 26-LEDset 27-LED-aux

$t_c = 80^\circ\text{C}$

Year — 8) Week — 9)

E 17 25

XXXXXXXXXX E1725 XXXXXXXXXX



B

Input⁶⁾ Output⁷⁾ **SELV**

1-Mains⁵⁾ 2-Mains 3-n/a 4-PE 5-n/a 6-DALI 7-DALI

Touch DIM

PE DA DA

LED+ LED- LEDset LED-aux

SEC U-OUT = 60V

21-LED+ 22-LED- 23-LED+ 24-LED- 25-n/a 26-LEDset 27-LED-aux

$t_c = 80^\circ\text{C}$

C


OTi DALI 80 1A6 OTi DALI 80 2A1




$I_{out} (R_{set})$ $I_{out} (R_{set})$

Output current [mA]

R_{set} [kOhm]

$I_{OUT[A]} = \frac{5V}{R_{set[\Omega]}} \times 1000$ (www.osram.com/ledset)



	OTi DALI 80 1A6	OTi DALI 80 2A1
B16 		13 x
B10 		8 x
		≤53 A
T_H		200 μ s
V_{NAC}	198–264 V	
V_{NDC}	176–276 V	
LEDset short	1400 mA	2100 mA

OSRAM

