

Cabinet workbench, series V

Worktop: Solid beech, 1,270 mm, 2 doors and vice



Application:

ANKE offers a wide range of high-quality workbenches, drawer cabinets and much more. See this quality for yourself - Made in Germany!

Execution:

- Robust welded sheet steel construction
- Stable bases made of square steel tube, 45 x 45 x 2 mm, with level compensation
- Drawers with 100 % full-extension slide, doors with 180° opening angle
- Can be used immediately, as it is delivered fully pre-assembled
- Vice, 100 mm jaw width with hinged lifter, can be rotated by 360° and height-adjustable. Vice compartment with doors.

Advantage:

- **Long-lasting:** 60 % greater glue surface due to special longitudinal bonding of the worktop
- **Robust:** Housing components with edges folded ten times, more folding increases resilience
- **Tested:** High levels of quality and reliability



Art. no.	50284 800
Number of drawers	0
Number of doors	2 PCS
Working height	850 mm
Worktop width	1270 mm
Worktop height	50 mm
Pullout type	Full extension
Worktop depth	700 mm
Colour of front	Gentian blue RAL 5010
Cabinet colour	Light grey RAL 7035
Levelling	Yes
Lock type	DOM® locking system
Model	800V
Surface	Powder-coated
Load-carrying capacity	1500 kg
Dynamic load-carrying capacity	450 kg
Type	With vice
Material of worktop	Solid beech
Material	Sheet steel
Central locking	Yes
Product Group	Prod. Gr. 502

EAN

4014641018849