

Drawer cabinets

Mobile with a pair of roller carriers and nylon rollers Ø 100 mm

LISTA
making workspace work

Application:

For day-to-day heavy-duty use in workshops

Version:

- All drawers with full extension
- Individual drawer lock as standard feature to prevent the cabinet from tipping over
- Perforated, slotted drawers provide a secure hold
- Very robust construction for a wide variety of applications and very demanding requirements

Advantage:

- Optimum wall height to keep items from falling out and getting lost
- Folding handle strips for simple, clean and protected labelling
- High quality - made in Germany and Swiss-made
- Runs perfectly smoothly and easily due to the lack of crossbars on the differential extension slide
- Full extension - clear overview and optimal access

Delivery:

1 anti-roll-off edging, 4-sided, 1 sliding rod, 1 roller carrier pair with nylon rollers Ø 100 mm



Art. no.	50301 365
Number of drawers	5 PCS
Height	962 mm
Width	717 mm
Depth	725 mm
Height x width x depth	962 x 717 x 725 mm
Housing height	700 mm
Draw width (inner dimension) x drawer depth (inner dimension)	600 x 600 mm
Load-carrying capacity per drawer	75 kg
Drawer lock	Single lock right
Drawer front height	1 x 50 mm, 2 x 100 mm, 1 x 150 mm, 1 x 200 mm
Cabinet colour	Light blue RAL 5012
Colour of front	Light blue RAL 5012
Cabinet equipment	Pair of castors
With sliding handle	Yes
Height of roller carrier pair	209 mm
Wheel diameter	160 mm
Material of wheel	Rubber
Information about the direction	Along
Load-carrying capacity of roller	600 kg
Opening/closing system	Key Lock
Rim height	53 mm
Clear height	600 mm
LISTA unit	36 x 36 E

EAN-Code

7612269063387