

Multipurpose meter MM 7-1

TRUE RMS digital multimeter/industry

BENNING

Application:

For use in installation fields/industry.

Delivery:

protective rubber frame, measuring leads, wire temperature sensor with adapter, bag



Art. no.	75024 231
Brand	BENNING
Manufacturer Part Number	044085
Model	MM 7-1
Display range	6000 digits
Measuring accuracy	+/- 0.08 %
Min./max. test voltage (DC)	10 μ V/DC-1000 V/DC
Min./max. test voltage (AC)	10 μ V/AC-1000 V/AC
Min./max. alternating current of measuring range	10 μ A-10 A
Min./max. direct current of measuring range	10 μ A-10 A
Continuity testing	Yes
Diode testing	Yes
Min./max. electrical-resistance measuring range	0.1 Ohm-40 MOhm
Min./max. frequency	0.00001 / 100 kHz
Min./max. temperature measuring range	-40 to 400 °C
Volt sensor	Yes
Memory function	HOLD, MAX/MIN
Measuring procedure	TRUE RMS
Overvoltage protection category	CAT IV/600 V, CAT III/1000 V
Length x width x height	190 x 94 x 48 mm
EN standard	61010
Gross Weight	0.806 kg
Product Group	7AH

EAN

4014651440852