



# MSR Gold™ MiniFastFit (DJ/Club)

## MSR Gold™ 300/2 MiniFastFit 1CT/4

Thanks to the specially designed lamp base and lamp holder, the MSR Gold™ MiniFastFit takes just seconds to replace, to help ensure non-stop clubbing entertainment. In addition, the innovative gold plated pins ensure excellent current transfer to prolong lamp and lamp holder lifetimes and thereby reduce lamp replacement costs. Easy handling and small compact fixture designs are allowed by the lamps compact size, while the very short arc provides a high perceived brightness and high beam intensity.

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data

General information		Correlated Color Temperature (Nom)	
Cap-Base	PGJX28 [ PGJX28]		9300 K
Operating Position	UNIVERSAL [ Any or Universal (U)]	Luminous Efficacy (Rated) (Min)	64 lm/W
Main Application	Entertainment	Luminous Efficacy (rated) (Nom)	71 lm/W
Life to 50% Failures (Nom)	750 h	Color Rendering Index (Nom)	80
System Description	MiniFastFit		
Light technical		Operating and electrical	
Color Code	2	Power (Nom)	300 W
Luminous Flux (Min)	19170 lm	Lamp Current (Nom)	3.75 A
Luminous Flux (Nom)	21300 lm	Ignition Supply Voltage (Min)	207 V
Chromaticity Coordinate X (Nom)	288		
Chromaticity Coordinate Y (Nom)	306	Controls and dimming	
		Dimmable	Yes

# MSR Gold™ MiniFastFit (DJ/Club)

Mechanical and housing	
Cap-Base Information	PGJX28
Luminaire design requirements	
Bulb Temperature (Max)	950 °C
Pinch Temperature (Max)	500 °C
Product data	
Full product code	87182912211100

Order product name	MSR Gold™ 300/2 MiniFastFit 1CT/4
EAN/UPC - Product	8718291221111
Order code	928177105115
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	4
Material Nr. (12NC)	928177105115
Net Weight (Piece)	0.062 kg

## Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)
MSR Gold™ 300/2 MiniFastFit 1CT/4	23 mm	5.0 mm	65.8 mm	67.8 mm	66.8 mm	126 mm

MSR Gold™ 300/2 MiniFastFit 1CT/4

