

---

## EFR-5/X 64620 HLX 150W 15V 20/CS 1/SKU



---

### Product features and benefits

- Precise filament alignment with patented quartz pinch technology
- OSRAM HLX lamps provide 10% higher luminous efficacy over standard halogen
- Instant on and nearly constant luminous flux over the life of the lamp
- Dimmable

---

### Areas of application

- Microscopy
- Laboratory & Analysis
- UV Curing
- Fiber Illumination
- Surgical & Dental Overhead
- Club & Disco

## Product datasheet

---

### Technical data

#### General product information

Product Number	54211
Product Name	EFR-5/X 64620 HLX 150W 15V 20/CS 1/SKU
Family Brand Name	XENOPHOT (HLX)
Application	Projector - 8mm
LIF Code	A1/232
Product Remark	- p (Operating Position) = Horizontal

#### Electrical data

Nominal Wattage	150 W
Nominal Voltage	15 V
Type of Current	AC

#### Light technical data

Working Distance a (in)	1.259 in
Working Distance a (mm)	32 mm
Average Rated Life	500 h

#### Physical attributes

Base	GZ6.35 BIPIN
Maximum Overall Length (in)	1.654 in
Maximum Overall Length (mm)	42 mm
Length l (in)	1.654 in
Length l (mm)	42 mm
Length l max. (in)	1.654 in
Length l max. (mm)	42 mm
Diameter d (in)	1.969 in
Diameter d (mm)	50.00 mm
Filament	C-8
Reflector Coating	50.00

#### Additional product data

Operating Position	p 90/15
Class	C (gas)

---

### Packaging Information

## Product datasheet

Product number	EAN/UPC	Packaging	Quantity	Outside dimensions L x w x h	Gross weight
54211	4050300797397	Folding box (SKU)	1	1.8 in x 1.8 in x 2.3 in	0.1 lb
54211	4050300797403	Shipping box (Case)	20	6.9 in x 4.8 in x 6.9 in	1.7 lb

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

---

### Disclaimer

OSRAM does not accept liability for errors, changes and omissions.