


Data Sheet

Type Number:	55630	
System:	Nickel Metal Hydride/ KOH Electrolyte	
Nominal Voltage [V]:	1.2	
Nominal Capacity C [mAh]:	280	
Typical Capacity C [mAh]:	300	
	at 56 mA / 1.00 V	
Weight, approx. [g]	11	
Dimensions [mm]:	min.	max.
Diameter [d]:	24.95	25.1
Height [h]:	6.95	7.55



UL Recognition:	MH 13654 (N)	
Coding:	Manufacturing 5 digit code (123 = day/4 = year/ 5 = version)	

Temperature Ranges [°C]	min.	max.
Storage: less than 30 days	-40	65
Discharge:	-20	65
Charge:	0	65

Charging Method:	
Normal Charging:	28 mA for 14 – 16 h
Accelerated Charging (20°C):	56 mA for 7-8 h
Fast Charging:	140 mA for 3 h *
	Time controlled, voltage control recommended
Trickle Charging:	8.4 mA

Overcharge (20°C):	28 mA continuous
	56 mA up to 1 year

Charge Retention [%] at 20°C:	90
	Capacity available after 1 month Storage at 20°C

Internal Resistance [Ohm]:	0.47
	at charged cells, 20°C, DC: 0.2 CA/2 CA, (IEC 61951-2)

Impedance [Ohm]:	0.08
	at charged cells, 20°C, AC: 1kHz, (IEC 61951-2)

Typical Capacities [mAh]:	
At 280 mA / 0.90 V	170

Max. Discharge Current (cont.) [mA]:	560
---	-----

Life Expectancy (typical):	
IEC Cycle:	1000 Cycles
Trickle Charge:	up to 6 years (20°C)
Trickle Charge:	up to 3 years (45°C)

* for fully discharged cells, 20 °C

Capacities based on normal charging