



GR 10-7 H7 S1.8

GROMMETS, NBR, SVART, TYP: YD: , ID:

Cable grommets to protect cables when insertion of cables through the holes for example in an apparatus box. Has good electrical insulation. Suitable for electric applications. Good resistance to oils and ozone.

Material: Polychloroprene rubber

Temperature range: -30 degrees Celsius to +90 degrees Celsius

Product Properties:

Dimensions:

Unit	pcs
h1	1.3 mm
$\varnothing B$	7 mm
$\varnothing d1$	10 mm
h	6.2 mm
$\varnothing d$	13.8 mm
MOQ	100 .

Approvals:

Compliance:

RoHS	RoHS 3 (2015/863)
Reach	No SVHC (Latest)

Other information:

Product Group	VET-grommets
Alternative SKU	GR10-7H7S1.8

Logistic information:

Barcode	733117614697
Country of origin	CN

Item status	Non Stock Item, can be on stock but is not a regular stock item.
Stock code	GR 10-7 H7 S1.8
Taric code	40169300
Unit	pcs
MOQ	100 .