

MILAN S.r.l. a socio unico

Head Office – Export department:
 Viale Europa, 74
 20090 Cusago (MI) Italy
 T. +39 02 9039.4556-4158
 F. +39 02 9039.4551
 www.taskercables.com

Ufficio Commerciale e Centro Distribuzione
 Viale Europa 72 Strada F12
 20090 Cusago (MI) Italy
 T. +39 02 9039.0037-0059
 F. +39 02 9039.0049
 www.tasker.it

Technical Datasheet



Halogen Free

Firestop®

tasker® TSK 1077 L.S.Z.H. – 1x0,26 mm² HDTV – HD SDI - Coaxial Cable 75 Ω



	A	B	C	D	E
--	---	---	---	---	---

CATEGORY Coaxial cable 75 Ω (See Video Catalogue)

- A:** Black Soft **L.S.Z.H.** sheath. - Outer Diam. Ø 4,00 (±0,20) mm.
- B:** First Shielding O.F.C. tinned copper Braid covering 95%.
- C:** Second Shielding in Aluminum foil tape, covering 100 %.
- D:** Core Insulation with Foam PE – Nom. Ø 2,60 (±0,20) mm.
- E:** Stiff Wire in O.F.C. Red Copper - formation 1x0,584 mm.
Nom. Cross section 1x0,26 mm².

MARKING

tasker® TSK1077 75Ω - 23 AWG O.F.C. – GAS INJECTED FHDPE – LSZH – BROADCAST COAX VIDEO HDTV / SDI CABLE

CUSTOM

This product is also available in **PVC, PE, PUR**, with or without **Steel Armor**.

Cable Properties

Conductor Resistance	66 Ω/Km ± 5%
Capacity Core/Shield	53,5 pF/mt
Velocity of Propagation	82%
Impedance	75 Ω
Nom. Delay	4,0 ns/m.
Operative Temperature	-30/+70°C

USE	X	Indoor	Interno Edificio	INSTALLATION	X	Fixed	Fissa	INFORMATION	X	RoHS2 Compliant
Impiego	X	Outdoor Limited	Esterno Limitato	Posa	X	Flexible Limited	Flessibilità limitata	Informazioni	X	Ver. C / 27.06.16
		Outdoor Direct Burial	Esterno Interrato		X	Dynamic (Drag Chain)	Mobile in Catena			
				Dynamic (Torsion)	Mobile in Torsione		