



Arax Belt

DER FLAMMFESTE HALTEGURT THE FLAME-RESISTANT WORK POSITIONING BELT

BESCHREIBUNG

Der Haltegurt ARAX BELT ist komplett aus flammfesten ARAMID gefertigt.

AUSSTATTUNG ARAX BELT

Verstellbare Steckschnallen
2 Befestigungsringe für Werkzeugtaschen
2 seitliche Halteösen
Flammfester Hüftpolster
Befestigungslasche für Abseilachter

TECHNISCHE DATEN

Norm: 358, EN 137, EN 15025
ARAX Belt: 0,61 kg
Gurt: Flammfestes ARAMID
Beschlage: Edelstahl
Temperatur: -35°C bis 170°C
Zersetzungstemperatur: 425°C

DESCRIPTION

The Work positioning belt ARAX BELT is manufactured completely from flame-resistant ARAMIDE.

EQUIPMENT ARAX BELT

Adjustable buckles
2 attachment rings for tool bags
2 lateral attachment points
Flame-resistant padding
Fastening loop for descent eight

TECHNICAL DATA

Standard: EN 358, EN 137, EN 15025
ARAX Belt: 0.61 kg
Belt: Flame-resistant ARAMIDE
Fittings: Stainless steel
Temperature: -35°C to 170°C
Decomposition temperature: 425°C



Das flammfeste Material ARAMID ist fur extreme Feuerwehr-Einsatze geeignet.
The flame-resistant material ARAMIDE is suitable for extreme firefighting intervention.

PRODUKT / PRODUCT

BEST. NR. / ART. NO.

ARAX Belt

Groe / size UNI

800750



Groe / size

UNI (S-XL)

Ø Huftgurt / waist belt

80 - 135 cm

Arax Connect

DAS FLAMMFESTE VERBINDUNGSMITTEL THE FLAME-RESISTANT LANYARD

BESCHREIBUNG

Der Haltegurt ARAX BELT und das Verbindungsmittel ARAX CONNECT sind komplett aus flammfesten ARAMID gefertigt.

AUSSTATTUNG ARAX CONNECT

AHK-Karabiner 4.000 daN
Gesamtlange: 0,75 m

TECHNISCHE DATEN

Norm: 358, EN 137, EN 15025
ARAX Connect: 0,36 kg
Gurt: Flammfestes ARAMID
Beschlage: Edelstahl
Temperatur: -35°C bis 170°C
Zersetzungstemperatur: 425°C

DESCRIPTION

The Work positioning belt ARAX BELT and the lanyard ARAX CONNECT are manufactured completely from flame-resistant ARAMIDE.

EQUIPMENT ARAX CONNECT

AHK-Karabiner 4.000 daN
Total length: 0.75 m

TECHNICAL DATA

Standard: EN 358, EN 137, EN 15025
ARAX Connect: 0.36 kg
Belt: Flame-resistant ARAMIDE
Fittings: Stainless steel
Temperature: -35°C to 170°C
Decomposition temperature: 425°C



PRODUKT / PRODUCT

BEST. NR. / ART. NO.

ARAX Connet 0,75 m

800751