




AVDAA031PLS0005H03

Connection technology



**Product characteristics**

Valve plug type A  
(according to DIN EN 175301-803)

Free from silicone

Free from halogen

with protective circuitry

**Electrical data**

Electrical design

Operating voltage [V]

AC/DC

24 AC/DC

Current rating [A]

5

Overvoltage protection VDR

•

**Environment**

Ambient temperature [°C]

-20...80

Protection

IP 67

**Mechanical data**

Design

angled

Material body

PP (polypropylene); Viton

Material nut

Brass; nickel-plated

Weight [kg]

0.252

**Displays / operating elements**

Output status indication LED

yellow

**Electrical connection**

Connection

PUR cable / 5 m; 3 x AWG 20 (3 x 0.5 mm<sup>2</sup>); Ø 6.6 mm; halogen-free



**Wiring**

Core colours

BN brown

BU blue

GN/YE green/yellow



**Remarks**

Pack quantity [piece]

1