

SIVACON sicube, door, right, with ventilation openings, IP40, H: 2200 mm, W: 900 mm, RAL 7035, safety class 1



Figure similar

Model	
Product brand name	SIVACON
Product designation	Door
Design of the surface	Powder-coated
Design of the product / EMC version	No
Protection class	
Protection class IP	IP40
Operating resource protection class	Safety class 1
Appearance	
RAL color number	RAL 7035
Color	Light gray
Product details	
Product component	
• ventilation	Yes
• Viewing door	No
• door for disconnecter lock	No

Mechanical Design

Height	2 200 mm
Width	900 mm
Opening direction of the door	right
Material	steel
Equipment marking	U UC
• acc. to DIN EN 61346-2	U
• acc. to DIN EN 81346-2	UC

EMC	Declaration of Conformity	Test Certificates	other
-----	---------------------------	-------------------	-------

[Miscellaneous](#)



[Special Test Certificate](#)

[Miscellaneous](#)

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8MF1290-2UT14-2BA2>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/8MF1290-2UT14-2BA2>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8MF1290-2UT14-2BA2

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



