



Order symbol: ARK14126CHFSSL
Product nbr: 8561570
Description: PC Enclosure
Remarks: Hinged opaque flat cover w/S.S. Lockable latch. Base includes 1/2 and 3/4 inch knock-outs

EAN: 6418074097460
EI. number:
Finland:

Including: Hinged cover. Base with 10-32 brass inserts, latched flat cover with formed in place PUR gasket, stainless hinge pin. Base with 1/2 and 3/4 inch knock-outs. Quick release latches. Enclosure mounting foot kit. Accessory 10-32 screws for panel mounting.

Sample photo

Dimensions:		Length	Width	Height	Accessories:	
mm:		305	254	127	ALBP1412	Aluminum Back Panel
inch:		12.0	10.0	5.0	ADFP1412	Dead Front Panel w/ screws
Materials:					ASP1412	Aluminum Swing Panel
Material:		Polycarbonate		ASPK1412	Swing Panel Kit incl. Panel	
Base colour:		RAL 7035 -light grey		ASPHK14	Swing Panel Kit w/o Panel	
Cover screws material:		Stainless steel		AMFL12	12" Mounting Flange Set	
Cover colour:		RAL 7035 -light grey		Rating:		
Gasket material:		Polyurethane		Ingress Protection (EN 60529): IP66/IP67		
Temperatures:					Impact Resistance (EN 62262): IK09	
Temperature °C (short term):		-40 ... 140 °C		Electrical insulation: Totally insulated		
Temperature °C (continuous):		-40 ... 80 °C		Halogen free (DIN/VDE 0472, Part 815): 1		
Temperature °F (short term):		-40 ... 284 °F		UV resistance: UL 508		
Temperature °F (continuous):		-40 ... 175 °F		Flammability Rating: UL 508		
Accessories:					Glow Wire Test (IEC 695-2-1) °C: 960	
ABP1412		Painted Steel Back Panel		NEMA Class: NEMA 4, 4X, 6, 6P, 12, 13		
Certificates:					Gost R	

