

**General Information** 

M4/6-RD **Extended Product Type:** 

Product ID: 1SNA105032R1500 EAN: 3472591050325

Catalog Description: M4/6

Long Description: M4/6-RD Screw Clamp Terminal Blocks Feed-through

Categories

Products » Low Voltage Products and Systems » Connection Devices » Terminal Blocks » Screw Clamp Terminal Blocks

**Ordering** 

EAN: 3472591050325 **Minimum Order Quantity:** 50 piece **Customs Tariff Number:** 85369010

**Dimensions** 

**Product Net Weight:** 8,7 g

**Container Information** 

50 piece Package Level 1 Units: Package Level 1 Width: 61 mm Package Level 1 Height: 47 mm 220 mm Package Level 1 Length: Package Level 1 Gross Weight: 0.44 kg 3472591050325 Package Level 1 EAN: Package Level 2 Units: 2000 piece Package Level 2 Width: 300 mm 300 mm Package Level 2 Height: 500 mm Package Level 2 Length: Package Level 2 Gross Weight: 18.1 kg **Product Packing Type:** Box

**Environmental** 

**RoHS Status:** Planned to follow EU Directive 2002/95/EC August 18, 2005 and amendment after 2006-05-

**Technical UL/CSA** 

V0 Flammability According to UL94:

**Additional Information** 

Color: red Connection Type: Screw clamp Dielectric Test Voltage: 3500 V Function: Feed-through

Level 0 - Information enabled **IIT Publishing Status:** 

Pollution Degree: 3 **Product Main Type:** M4/6 **Product Name:** Terminal block

Rated Impulse Withstand Voltage

(U<sub>imp</sub>):

4 mm

Recommended Screw Driver: Spacing: 6 mm **Sub-Function:** 2 connections

**Tightening Torques:** acc. IEC 60947-1 0.5 N·m Manufacturer 0.8 N·m

Wire Stripping Length: 9.5 mm

Certificates and Declarations (Document Number)

1SND225001C1000 **Declaration of Conformity - CE: GOST Certificate:** 1SND161005A1103

Classifications

**Object Classification Code:** Χ











