

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [5054483071](#)
Status: **Active**
Overview: [Micro-Lock Plus Wire-to-Board Connector System](#)
Description: [Micro-Lock PLUS Right Angle Header, 1.25mm Pitch, Dual Row, Tin-Bismuth Plating, 30 Circuits, Black](#)

Documents:

3D Model	Application Specification AS-505432-002-001 (PDF)
Drawing (PDF)	Packaging Specification 5054489200-200 (PDF)
Product Specification 5054320000-002 (PDF)	RoHS Certificate of Compliance (PDF)
Application Specification AS-505432-001-001 (PDF)	Product Literature (PDF)

Agency Certification

UL E29179

General


Product Family	PCB Headers
Series	505448
Application	Signal, Wire-to-Board
Overview	Micro-Lock Plus Wire-to-Board Connector System
Product Literature Order No	987651-4888
Product Name	Micro-Lock PLUS
UPC	889056387897

Physical

Breakaway	No
Circuits (Loaded)	30
Circuits (maximum)	30
Color - Resin	Black
Durability (mating cycles max)	30
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	Yes
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin-Bismuth
Material - Plating Termination	Tin-Bismuth
Material - Resin	Polyamide
Net Weight	2498.905/mg
Number of Rows	2
Orientation	Right Angle
PCB Locator	No
PCB Retention	Yes
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	1.25mm
Pitch - Termination Interface	1.25mm
Plating min - Mating	1.000µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Stackable	No
Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	-40°C to +105°C
Termination Interface: Style	Surface Mount

Electrical

Current - Maximum per Contact 1.5A



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per

-ED/01/2018 (15

January 2018)

Halogen-Free

Status

Not Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com

Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[505448](#) Series

Mates With

[Micro-Lock PLUS Receptacle Housing 505432](#)

Voltage - Maximum

50V AC (RMS)/DC

Material Info

Reference - Drawing Numbers

Application Specification

AS-505432-001-001, AS-505432-002-001

Packaging Specification

5054489200-200

Product Specification

5054320000-002

Sales Drawing

5054480000-000, 5054480001-000

This document was generated on 07/31/2018

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION