

MAX430S Orange

- Waterproof and dustproof IP67 certified
- Mil Specs (STANAG 4280, DEF STAN 81-41)
- Watertight seal around lid
- Automatic pressure release valve
- Easy to open double throw latches
- Load tested soft grip handle
- Holes for double padlocking
- Holes for shoulder strap
- Stackable interlocking system
- Thick body material
- Extra fixing points
- Fully length hinges
- Nylon pins, corrosion free

Body and handle: polypropylene copolymer

Latches: nylon

Pins: nylon + 30% fiberglass

O-ring: polymer

COLOURS: black, orange, sahara

EXTERNAL DIMENSIONS 464 x 366 x H176 mm (18.27 x 14.41 x H6.93 inch)

INTERNAL DIMENSIONS: 426 x 290 x H159 mm (16.77 x 11.42 x H6.26 inch)

LID-BOTTOM DEPTH: 45 + 114 mm (1.77 + 4.49 inch)

WEIGHT WITH FOAM: 3.04 kg – 6.70 lbs.

CAPACITY: 20kg – 44 lbs.

CARTON DIMENSIONS: 490 x 380 x 375mm – 19.29 x 14.96 x 14.76 inch

PCS PER CARTON: 2

WEIGHT OF THE FULL CARTON WITH FOAMS: 6.95 kg – 15.32 lbs.

MOULDING: injection molded

RANGE TEMPERATURE: -30 / 90°C (-22 / 194°F)

FEATURES: IP67, DEF STAN 81-41, STANAG 4280

CUSTOMIZATION: personalized nameplate/resin label

ACCESSORIES: cubed foams, lid organizer, padded dividers, padded shoulder strap, pouch

