


Blacklight BL368 Toughcoat T5

F8W T5 BL368 Toughcoat™
0001648



Product features

- Excellent fragment retention in the event of breakageThe protective FEP coating meets the IEC60068-2-75 Pendulum Hammer test (5 Joule) and the 4m drop test, demonstrating excellent glass retention in the event of accidental lamp breakageThe 97% UV-A transmission of FEP maintains maximum insect attraction



PRODUCT OVERVIEW

Product name	F8W T5 BL368 Toughcoat™
Technology	Special applications
Lamp shape	Tubular shape
Type	T5
Cap/Base	G5
Lamp finish	Frosted/Coated
Fixture rating	Enclosed
General application	SPG
ETIM Class	EC002962
E-number FI	4940438
Light colour	BL368 Blacklight
Wattage (W)	8.00
Product Voltage (V)	56
Dimmable	No
Dimming method	N/A
Average life (Nominal) (h)	10000
Product EAN number	5410288016481

DATA TABLE

General data

Product name	F8W T5 BL368 Toughcoat™
Technology	Special applications
Lamp shape	Tubular shape
Type	T5
Cap/Base	G5
Lamp finish	Frosted/Coated
Fixture rating	Enclosed
General application	SPG
Operating temperature range (°C)	-15°C...+50°C
ETIM Class	EC002962
E-number FI	4940438

Optical data

Blacklight BL368 Toughcoat T5

F8W T5 BL368 Toughcoat™
0001648

Ambient temperature for maximum luminous flux (°C)	25
Light colour	BL368 Blacklight
Adjustable chromaticity	N

Electrical data

Wattage (W)	8.00
Current (A)	0.145
Mains voltage (V)	230-240V
Product Voltage (V)	56
Control gear required	Yes
Transformer required	No
Dimmable	No
Dimming method	N/A
Drive current (mA)	145

Lifetime data

Average life (Nominal) (h)	10000
----------------------------	-------

Physical data

Nominal Product Length (mm)	300.0
Nominal Product Diameter (mm)	16
Max. Length base to base (mm) - A	288.3
Length base to pin Min-Max (mm) - B	293.0-295.4
Max. Lamp Length (mm) - C/L	302.5
Max. Lamp Diameter (mm) - D	17.0
Weight (kg)	0.023

Packaging

Single packaging type	Carton
Product EAN number	5410288016481
Packaging single length / height (cm)	30.3
Packaging single width (cm)	1.9
Packaging single depth (cm)	1.9
DUN14 (outer)	15410288016488
Units per outer package	25
Packaging outer length / height (cm)	32.0
Packaging outer width (cm)	11.0
Packaging outer depth (cm)	10.5

Safety data

Lamp mercury content (mg)	2.30
Optimal operating condition (°C)	-15-50
Breakage cleaning instructions	Applicable
Recommendation for disposal at end of life	Applicable
Special purpose lamp	Yes
Intended purpose	Flykilling - Insect attraction
Suitable for household illumination	No

Blacklight BL368 Toughcoat T5 *F8W T5 BL368 Toughcoat™* 0001648

Safety message

Not suitable for household

PHOTOMETRY

